

⋮ FA60

FLUKO®

High Shear Dispersing Emulsifier

Description

The laboratory pilot equipment can accurately complete the production simulation from the small test to the industrialization, which provides the basis for testing the production process and selecting the large production equipment. A variety of process requirements can be achieved simply by changing the agitator. The machine has integrated control, variable frequency speed regulation, speed display, electric lifting and other functions.

Applicable

Pilot for high efficiency stirring, dispersing, homogenizing, emulsifying, strong mixing, solid-liquid mixing and other processes.



FA60

High Shear Dispersing Emulsifier



Order

6261161

Optional Agitators

Model	FA60
Motor power	750W
Power supply	220V , 50Hz
Working capacity(H ₂ O)	5-30L
Maximum working viscosity	5000cP
Speed range	300-6000rpm
Speed display	Digital display
Speed control	Frequency control
Medium-contact material	SS316L
Shaft sleeve material	PTFE
Standard dispersing agitator	60F
Permissible temperature range	5-40°C
Permissible humidity range	80%
Protection grade for motor hood	IP54
Inverter	Standard
Overload protection	Yes
Process type	Batch processing
Work frame, stand base	Electric lifting
Work frame, stand base material	SS304
Lifting range	360
Overall dimensions	500×400×915
Weight	~35kg
Package	Wooden case

Order #>Model			
			
	171	211	161
	60G	60M	60F
			
	191	193	194
	60J	60JQ	60JX
			
	201	231	221
	60PJ	60T	60C

Biology
Pharmacy

Food

Daily Care

Chemical
Industry

New
Material



FLUKO EQUIPMENT SHANGHAI CO., LTD.
#21-22 NO. 300, Shunda Road, Jiading, 201802, Shanghai, China
Phone +86 21 230 993 68, Fax +86 21 510 103 68
sales@fluko.com , www.fluko.com